




FLEX³PRO Flexo System Analyzer



**Accurate and repeatable measurements
on Flexo Plates and Print.**



Measure

Film
Laser Mask
Flexo Plate
Print



Messen

Film
LAMS Maske
Flexoplatte
Druck



Misurare

Pellicola
Polimero con LAMS
Polimero
Stampa



Meurer

Film
Plaque masquée
Plaque Flexo
Imprimé



Medir

Película
Mascara LAMS
Polímero Flexo
Impresión

Verify

Dot Area
Screen Ruling
Bar Code Width
Dot Shape
Stain Density

Prüfen

Flächendeckung
Rasterweite
Linienbreite
Punktaufbau
Grundschleier

Verificare

Area di punto
Lineatura
Larghezza linea
Struttura del punto
Densità Stain

Vérifier

surface du point%
Trame
Largeur de la ligne
Structure du point
Densité Stain

Verificar

Area del punto
Trama/ Lineatura
Ancho de linea
Estructura del punto
Velo de densidad

Analyze

Full Stochastic Screen
40LPI to 400LPI
Minimum Dot

Analysieren

FM-Raster
40LPI bis 400LPI
Kleinste Punkte

Analizzare

Stochastico
18LPI a 400LPI
Punto minimo

Analyse

Trame stochastique
18LPI to 400LPI
Point plus petit

Analizar

Trama estocástica
40LPI hasta 400LPI
Punto menor

Documentation

Statistic
Quality Reports

Dokumentation

Statistik
Prüfberichte

Documentazione

Statistica
Relazione di Qualità

Documentation

Statistique
Fiche de contrôle en PDF

Documentación

Estadística
Reporte de calidad en PDF

Calibrate

Reference on Glass

Kalibrieren

Referenz auf Glas

Calibrare

Referenza su vetro

Calibrage

Référence sur verre

Calibrar

Referencia sobre vidrio

FLEX³PRO Flexo System Analyzer



Software Fleye³ included

Sample Types

Transparent Flexo Plates
Ablation Mask
Film
Non transparent Flexo Plates
Offset Plates
3D View Analysis
Print sample





Functions Set

Dot Area%
Auto Screen ruling
Dot diameter
Dot surface area
Dot perimeter
Edge factor
Stain density
Line width
Line quality index
Dot structure index
Dot height
Dot 3D diameter
Dot shoulder angle
Dot relief depth
Dot void factor
Slur factor
Mottle

Feature Set

Copy&Paste Images and Data
Compare Images
Digital Zoom x4
Dot cross section
CYM color separation
Screen angles
Mottle structure analysis
Print reports
Statistics

Find your
minimum
Dot!



Optionals for Flexo³Pro



SLEEX

Sleeve Adapter
for easy positioning



ROUND

Sleeve Station
for transparent Flexo Sleeves



RELIX
Relief Measurement
a Rount Optional



FLEYE+

Fast Quality Reports
Software Module